





Pharmaceutical Educational Factory Devices Ahram Canadian University

أجهزة مصنع الأدوية التعليمى بكلية الصيدلة جامعة الأهرام الكندية

UHPLC with quaternary pump, thermostatted auto-injector, column compartment, and DAD, RID and FLR detectors



Distek **Digital tablet tester**, to automatically measure tablet thickness, weight and breaking force with load cell of 500 N with display accuracy of 0.1 N with IQ, OQ, DQ Documentation





Copley Hardness tester



Copley **Friability tester** (dual drum plus abrasion drum), with variable from 20-70rpm ± 1 rpm with recording timer and it operates at 10° angle to test larger tablets





Copley **Tablet disintegration tester** with stroke ,(dual racks)
height of 55mm and 30 strokes /
min with online validation of
strokes per minute and with
normal basket racks,
baskets "B"suppository and
with three larger test tubes. It
has a LCD and IQ/OQ/OQ
.Documents



